


# Roller/ Solar Minimum Mounting Depth Requirement

Product ID: 545483, 545484, 545485


## Semi Inside Mount



Partially Protruding Out  
of the Window Opening

Lift System	Top Treatment	Single Shade (in)	Dual Shade (in)
Continuous Cord Loop*	None	3 1/4	2 3/4 with raceway or valance only
	Fascia/ Valance/With Raceway	2 7/8	
SmartRelease™	Fascia/ Valance/With Raceway	2 7/8	
Cordless	None	3 1/8	
	Fascia/ Valance/With Raceway	2 5/8	
Motorization*	None	3 1/4	N/A
	Fascia/ Valance/With Raceway	2 3/4	

## Inside Mount



Flush with the Window Opening

Lift System	Top Treatment	Single Shade (in)	Dual Shade (in)	
Continuous Cord Loop*	None/ With Raceway	3 7/8	3 7/8 with raceway	4 5/8 with valance
	Fascia/ Valance	4 3/4		
SmartRelease™	With Raceway	3 7/8		
	Fascia/ Valance	4 3/4		
Cordless	None/ With Raceway	3 1/2	N/A	N/A
	Fascia/ Valance	4 5/8		
Motorization*	None/ With Raceway	3 5/8		
	Fascia/ Valance	4 5/8		

\* Coupled shades are available for these lifts and have the same depth as single shade.

*Note: Inside Mount depth may be slightly different depending on the window size and the fabric.*

*The above measurements are rounded to provide a simplified version. Please refer to the spec book for the exact minimum depths.*